



# RFM700-M Series Digital Refractometers

EASY TO USE ATC REFRACTOMETERS FOR USE IN HARSH FACTORY ENVIRONMENTS



RFM700 series refractometers are robust, low cost, fully automatic instruments that are ideally suited to the food, sugar and beverage industries but can also be used in many other non-food applications where temperature control is not required.

Commonly, the RFM700-M series refractometers are supplied to operate in the °Brix scale with results temperature compensated to 20 °C in accordance with ICUMSA.

Additional user scales provide measurement in different formats such as Refractive Index (RI) various wine, urine specific gravity & automotive scales as well as allowing custom scales to be loaded in accordance with product data.

Ideal for use in busy laboratories or harsh factory environments.

# **Key Features Included as Standard**


- Classic red or modern colour display
- Auto-sense "hands free" measurement
- Simple audit trail (date, time & batch no.)
- Alpha-numeric keypad for easy data entry
- Flat sapphire prism surface for easy-cleaning
- USB connectivity





# RFM700-M Digital Refractometers ROBUST & SIMPLE TO USE DIGITAL REFRACTOMETER







### **Software Features**

- Choice of 7 languages
- Save over 8000 readings
- Reading, user & config audit trails
- Print to secure PDF
- Onboard user scale library
- User maintenance prompts
- Easy to use Installation Wizard



Specifications	RFM712-M	RFM732-M	RFM742-M
Order Code	19-00	19-10	19-20
Scales			
°Brix	0-50	0-100	0-100
Refractive Index	1.33-1.42	1.33-1.54	1.33-1.54
User Defined (RI equivalent)	2	2	2
Resolution			
°Brix	0.1	0.1	0.01
Refractive Index	0.0001	0.0001	0.00001
Accuracy			
°Brix	±0.1	±0.1	±0.04
Refractive Index	±0.0001	±0.0001	±0.00005
Precision (Reproducibility)			
°Brix	± 0.05	± 0.05	± 0.01
Refractive Index	± 0.00005	± 0.00005	± 0.00001
Temperature Range			
Ambient	5-40 °C		
Sample	5-95 °C		
Peltier	ATC only		
Temperature Compensation			
Sucrose (°Brix)	5-80 °C		
AG Fluids (°Brix)	10-40 °C		
User	Simple coefficie	ent (units/ °C) or po	lynomial function
Temperature Sensor Accuracy	±0.05 °C	±0.05 °C	±0.05 °C
Temperature Stability Checks	None/Delay Tir	ne (programmable	in seconds)
Peltier Control Stability	ATC only	ATC only	ATC only
Humidity Range	<90% RH (non	condensing)	
Prism Seal	Silicone/Resin	Silicone/Resin	Silicone/Resin
Interfaces	1 x USB (A), 1 x	Ethernet, RS232 vi	ia optional USB adapto
Power		V DC, ±5%, <2A 00-240V, 50-60Hz	(supplied)

## **Order Codes**

Code	Description
19-00	<b>RFM712-M refractometer</b> with integral 4" full colour display, robust switch membrane and USB connectivity. Supplied with instruction manual and certificate of conformity.
19-10	<b>RFM732-M refractometer</b> with integral 4" full colour display, robust switch membrane and USB connectivity. Supplied with instruction manual and certificate of conformity.
19-20	<b>RFM742-M refractometer</b> with integral 4" full colour display, robust switch membrane and USB connectivity. Supplied with instruction manual and certificate of conformity.

### Bellingham + Stanley, a Xylem brand

Xylem, Longfield Road Tunbridge Wells TN2 3EY United Kingdom

**(S)** +44 (0) 1892 500400

sales.bs.uk@xylem.com
www.bellinghamandstanley.com

### **Bellingham + Stanley (USA)**

Xylem 1700/1725 Brannum Lane Yellow Springs OH 45387

+1 (937) 688 4255

sales.bs.us@xylem.com